Acme Sanitary Ware Co Ltd

Acme Building, 22-28 Nanking Street, Kowloon, Hong Kong Fax: 2710 8012 Tel: 2388 7171 E-mail: acme@acmesanitary.com.hk Website: www. acmesanitaryware.com.hk

PROJECT	REF	REV	ITEM CODE	
LOCATION	DATE		PAGE	

SANITARY WARE SPECIFICATION SHEET

Item Descriptions Mediclinics "Dualflow®Plus" (Spain) ABS

sensor operated hand dryer in white finish

Dimensions L320 x W228 x H665 mm

M24A Model

Material/Finish ABS / White Finish

Manufacturer Mediclinics, S.A. (Spain)

Supplier Acme Sanitary Ware Co. Ltd

Mr. Eric Wong/ Mr. Don Yuen

Contact Tel/Fax (852) 2388-7171 / (852) 2710-8012

E-mail acme@acmesanitary.com.hk Website www.acmesanitary.com.hk

General description

- Automatic double-sided high-speed hand dryer with maintenancefree brushless motor, ensuring long lifespan, ideal for an intensive usage and, therefore, suitable for high traffic facilities.
- Water collection area with no-splash design, which prevents the residual water from drying hands to end up on the floor, thus keeping it dry and preventing slipping hazard.
- · Dualflow Plus is a touchless hand dryer because it starts and stops automatically thanks to a pair of lR sensors in both sides of the device for automatic hands detection, creating, therefore, theoptimal hygienic conditions because it confines the growth of bacteria.
- · It incorporates an HEPA filter media that filters the solid particles in suspension (pollen, dust mites, tobacco smoke, etc.) significantly improving air quality.
- · Proven antimicrobial and antibacterial protection using silver ion technology from Biocote®, providing a total antimicrobial solution. These ions inhibit the reproduction of micro-organisms in the product throughout its lifetime.
- · Universal voltage. It works indistinctly at electrical voltages of100-120 V or 220-240 V.
- · Motor power adjustable, allowing electricity consumption to be regulated (between 250 and 1,100W).
- Maximum air speed 410 Km/h.
- Dries hands in only 8 / 15 seconds.
- 30 second maximum continuous running time.
- Lowest noise level in its category. (62 dBA in ECO mode).




M24A White finish



M24AB



Satin finish



Technical Specifications

•	
Voltage	100 - 120V / 220 - 240V
Frequency	50/60Hz
Electrical Isolation	Class I
Total power	250 – 1,100W
Consumption	1.3 – 4.8A
Motor power	900W
Rpm	17,600 – 27,600
Heating element power	200W or OW (ON/OFF switch)
Dimensions	665x320x228 mm
Weight	8.5Kg
Cover thickness	3mm
Drying time	8-15sec
Effective airflow	101 - 177 m³/h (1,680 - 2,950 l/min)
Air velocity	234 – 410Km/h
Air temperature (10 cm	38°C
distance/23ºC)	
Sound pressure (at 2m)	62 – 72dBA
Protection rating	IPX4

Note: YouTube https://youtu.be/ICMFlGHJzDk











Acme Sanitary Ware Co Ltd



Acme Building, 22-28 Nanking Street, Kowloon, Hong Kong Tel: 2388 7171 Fax: 2710 8012 E-mail: acme@acmesanitary.com.hk

Website: www. acmesanitaryware.com.hk

PROJECT	REF	REV	ITEM CODE	
LOCATION	DATE		PAGE	

SANITARY WARE SPECIFICATION SHEET


Components and materials

- **COVER**: made of high impact ABS, 3 mm thick.
- BASE PLATE: made of plastic PA6V0.


- Codes Cover material Cover finish M24A ABS White M24AB ABS Black M24ACS ABS
- MOTOR: extremely durable high-speed Class F brushless motor, maintenance free, with adjustable power, allowing electricity consumption and sound pressure to be regulated.
- · HEATING ELEMENT: minimum waved wire NiCr heating element of 200W, mounted on a mica frame that incorporates a self-resetable thermal cut-off which disconnect the whole appliance. The heating element can be disconnected by means of an ON/OFF switch.
- · HEPA FILTER MEDIA: cartridge that holds an HEPA filter mediathat filters suspended solid particles (pollen, dust mites, cigarette smoke, etc.), notably improving the air quality. Furthermore, this cartridge also contains and activated carbon filtering mediathat neutralizes odours and absorbs fumes and gases, helping avoid bad odours.
- INNER TANK: collects the water. It is removable and it has an external valve for easy emptying.
- AUTO CHECK-IN LIGHTING PANEL: for fast diagnosis of the dryer (green -machine running, blue -full tank, red -check engine). Optical and acoustic warning of full tank.
- **ODOR NEUTRALIZER**: for a cleaner and more pleasant atmosphere in the bathroom. (optional).

Place the hands between the air outflow valves, inside the hand dryer. The dryer will start automatically, and go on with no interruption as long as the hands are kept in the detection range of the sensor. Move the hands vertically in order to dry them completely. The appliance will stop 2 seconds after the hands are removed

Mounting (Recommoended heights distance form the floor)







$$H = {}^{85 \text{ cm}}_{(33 \text{ 1/2"})}$$

$$y = {57 \text{ cm} \atop (22 \text{ 1/2"})}$$



87 cm (34 1/4")

80 cm $(31\ 1/2")$

52 cm $(20 \ 1/2")$





Heating element ON/OFF switch Option to turn ON/OFF the heating element



Heating element For a maximun comfort



HEPA filter media clans the air stopping the particles of dirt, dust, bacteria, pollen, etc. Clean and fresh air.



Note: YouTube https://youtu.be/ICMFlGHJzDk











Acme Sanitary Ware Co Ltd

Acme Building, 22-28 Nanking Street, Kowloon, Hong Kong
Tel: 2388 7171 Fax: 2710 8012
E-mail: acme@acmesanitary.com.hk

Website: www. acmesanitaryware.com.hk

HAND DRYERS

Table

	MODEL	MOITA	DIMINENSIONS	Taoi		a)	ADJUSTABLE MOTOR			TRAFFIC FREQUENCY				
	IVIODEL	OPERATION		DIMINITENSIONS	je l	HEPA filter media	Drain Pipe	ADJUSTABLE POWER		WOTOR		IKAFF	IC FREQ	DENCY
		manual	sensor	(mm)	lonizer	EPA	aj.	TOWER.	induction	brush	brushless	HIGH	MEDIUM	LOW
	ah sa lili as sa a					Ξ	۵							
	dualflourp	lUS	_									ualfla	urplus	
	M24A M24AB		•	1	*	•	8				•			
l'	M24ACS				*	÷	*					÷		
	M14A		•	L320xD228xH665	*	•	*	•		•		•		
	M14AB		•			•		•		•		•		
	M14ACS	lun La	0		*	•	0	•		•	- h (1 1 -	0	- L 0	
	mochflow p	xw•	8	8		•		mo	chflow plu	Js / mc	chilom			
	M19AB				*	8								
	M19AC		•		*	*		•			•	•		
	M19ACS		•	L213xD170xH330	*	*		•			•	•		
100	M09A		•		*	*		•		•		•		
_	M09AB M09AC		•	1	8	8		•		•		•		
	M09ACS				*	8				·		÷		
	speedflou	r plus	_	dflow					S		ow plus/		flow	
	M17A		•		*	•		•		•		•		
darr.	M17AB		•		*	•		•		•		•		
	M17AC M17ACS		•		*	•		•		•		•		
-	M17ACS			1200-0100	*	÷		•		•		÷		
	M06A		•	L290xD100xH270 (INSIDE CABINET)				•		•		•		
	M06AB		•					•		•		•		
	M06AC		•					•		•		•		
	M06ACS M06AF		•	-				•		•		•		
	saniflow*							_					niflow•	
The same of	E05	•								•		•		
	E05B	•		L276xD214xH245						•		•		
1 Sign	E05C E05CS	•								•		•		
	E85	•		L282xD215xH255						•		•		
	E88	•		LEGENDEISKIIESS						•		•		
	E88B	•								•		•		
	E88C	•		L278xD212xH248						•		•		
	E88CS E88O	•		-	_					•		•		
	E05A	•	•		•					•		•		
	E05AB		•	L276xD214xH245	•					•		0		
	E05AC		•		•					•		•		
gard min	E05ACS		•		•					•		•		
	E85A E88A		•	L282xD215xH255	•					•		•		
	E88AB		•		·					·		•		
	E88AC		•	L278xD212xH248	_					0		•		
	E88ACS		•		•					•		•		
	E88AO modificus		•		•					•		o mev	diflow	
	mediflow• M02A		•		•					•		me	o o	
0-	M02AB		•		÷					·			•	
	M02AC		0	1 1	•					•			0	
	M02ACS		•	L275xD164xH325	•					•			0	
	M03A M03AB		•		•					•			•	
	M03AC		•		•					·			•	
	M03ACS		•		•					•			•	
-	optima											0)	otima	
	M99A		0	L260xD150xH302	0				0				0	
	M99AC		0		0				0				0	
	M99ACS		0		0		_		0			iv	vionolus	
	M88APLUS		0	L253xD150xH303	0				0			Jul	0	
3	M88PLUS	0		L253xD150xH303					0				0	
	smartflow											sm	artite	IUUF
	M04A		0		0					0				0
5.	M04AC		0	L147xD138xH259	0					0				0
U-in	M04ACS		0		0	ational				0				0