

## Acme Sanitary Ware Co. Ltd.


1/F, Acme Building, 22-28 Nanking Street, Kowloon, Hong Kong Tel: 2388 7171 Fax: 2710 8012 Email: acme@acmesanitary.com.hk Since 1949 Website: www.acmesanitary.com.hk



PROJECT	REF	REV	ITEM CODE	
LOCATION	DATE		PAGE	

### SANITARY WARE SPECIFICATION SHEET

Item Descriptions	Inax (Japan) Chrome plated deck mounted Infra-red sensor faucet; DC Supply with 4x AA size alkaline cell battery
Dimensions	L108 x W51 x H138 mm
Model	AM-300C
Finish	Chrome Plated
Manufacturer	Inax (Japan)
Source	Acme Sanitary Ware Co. Ltd Mr. Eric Wong/ Mr. Don Yuen
Contact Tel/Fax	(852) 2388-7171 / (852) 2710-8012
E-mail	acme@acmesanitary.com.hk
Website	www.acmesanitary.com.hk



•Not included drain pop-up

•Power: Aqua Energy Hydraulic Generator: DC7V

•Back-up: 4x AA size alkaline cell battery

•Water pressure: 0.05MPa (Flow) to 0.75MPa (Static)

•Ambient Temperature: 0 to 40 degrees Celsius •Ambient Humidity: Not higher than 90 %RH

•Flow Rate: 2 to 3 L/min (with flow restrictor @2.5 L/min)

•Sensing: Distance-measuring IR sensor •Sensing Distance: Automatically Adjusted •Size Of Sensing Area: Dia. 10 mm

•Inlet Connection: Single: R1/2 / Thermostatic: PJ 1/2 screw

	仕 様				
電源	主電源	DC7V(電源回路)			
	バックアップ	DC3V(アルカリ乾電池単3形4本)			
使用圧	力範囲	0.05(流動時)~0.75(静止時)MPa			
使用水		水道水および飲用可能な井戸水			
使用環	境温度範囲	0~40°C			
使用環	境湿度範囲	90%RH以下			
適正流	量範囲	2~3L/分(2.5L/分定流量弁内蔵)			
感知方	式	距離測定式赤外線センサー			
感知距	離	自動設定(感知距離自動調整機能内蔵)			
感知エ	リア幅	約Ø10mm			



<sup>\*</sup> All information of the above is for the reference only. No prior notice is made if any changes.




# Acme Sanitary Ware Co. Ltd.

1/F, Acme Building, 22-28 Nanking Street, Kowloon, Hong Kong Tel: 2388 7171 Fax: 2710 8012  ${\bf Email: acme@acmesanitary.com.hk}$ Since 1949 Website: www.acmesanitary.com.hk



PROJECT	REF	REV	ITEM CODE	
LOCATION	DATE		PAGE	_


### SANITARY WARE SPECIFICATION SHEET



番号	部品品番	部品名	所要 数
1	A-11018-50	吐水□ASSY	1
2	A-8216	45°維手ASSY	1
3	A-11028	機能BOX	1
4	72-1057	クイックアスナー (呼び12.7)	1
5	A-8187	定流量弁ASSY	1
6	A-8185	止水栓ASSY	1
エ	KG-23	締付工具 (対辺13)	1



#### 単水栓の場合



1.マイナスドライバーなどで止水栓を矢 印の方向いっぱいにまわす。センサー に手をかざし、水が止まったことを確 認する。

Note: